


RoHS Compliant

UP-880

uPCI 2xRS232 POS 1A

"SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"



Description

Universal PCI providing two Powered RS232 serial ports. Data transfer rates up to 115,200 baud rates and the 128 byte deep transmit and 128 byte receive FIFOs, coupled with 1Mbit/s line drivers deliver uncompromising performance for your electronic point of sale ePOS device. The power supplied on the RS232 port is selectable. Ground or 12V can be selected on pin 1 of each port and also 12V or 5V can be selected on pin 9 of each port. Powered Universal PCI cards are ideal for connecting and powering peripherals such as bar code readers, printers, card readers, display units and other Point Of Sale devices. Maximum power output is 1 Amp. Includes drivers for all Windows 32 bit and 64 bit Operating Systems, including Windows 7.

Features

- 2 port RS232
- 128 Byte Tx and 128 Byte Rx FIFOs
- Up to 115,200 Baud
- DB9 connector (9 Pin Male)
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)

Options



UP-880:
uPCI 2xRS232 POS 1A


Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows 7 32 bit 64 bit Editions
- Windows Server 2008 32 bit 64 bit Editions
- Windows Vista 32 bit 64 bit editions
- Windows Server 2003 32 bit 64 bit Editions



As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.



ORDER

Description

uPCI 2xRS232 POS 1A


Code

UP-880



uPCI 2xRS232 POS 1A

UP-880 Full Specification

Port <table><tr><td>Pin 1</td><td>DCD/12V/GND</td></tr><tr><td>Pin 2</td><td>RXD</td></tr><tr><td>Pin 3</td><td>TXD</td></tr><tr><td>Pin 4</td><td>DTR</td></tr><tr><td>Pin 5</td><td>GND</td></tr><tr><td>Pin 6</td><td>DSR</td></tr><tr><td>Pin 7</td><td>RTS</td></tr><tr><td>Pin 8</td><td>CTS</td></tr><tr><td>Pin 9</td><td>RI/12V/5V</td></tr></table> Powered RS232 Pinout (9 Pin Male) 	Pin 1	DCD/12V/GND	Pin 2	RXD	Pin 3	TXD	Pin 4	DTR	Pin 5	GND	Pin 6	DSR	Pin 7	RTS	Pin 8	CTS	Pin 9	RI/12V/5V	Ports Connector FIFO size Operating Distance Cable	2 x RS232 DB9 Connector - 9 Pin Male 128 RX FIFO + 128 TX FIFO EIA - RS232 Standard No Cable; Integrated Connector
Pin 1	DCD/12V/GND																			
Pin 2	RXD																			
Pin 3	TXD																			
Pin 4	DTR																			
Pin 5	GND																			
Pin 6	DSR																			
Pin 7	RTS																			
Pin 8	CTS																			
Pin 9	RI/12V/5V																			
Port Settings 115,200  baud	Baud Rate Data Bits Parity Stop Bits Flow Control Tx/Rx Modes	115,200 5,6,7 or 8 Odd, Even, None, Mark or Space 1, 1.5 or 2 Point to Point																		
Interface	OS Compatibility BUS	Microsoft Windows 7 32 bit 64 bit Editions Windows Server 2008 32 bit 64 bit Editions Windows Vista 32 bit 64 bit Editions Windows Server 2003 32 bit 64 bit Editions Windows XP 32 bit 64 bit Editions Microsoft Windows 2000 Microsoft Windows 98 PCI Powered :																		
Approvals	Industry Approvals Microsoft Approvals	AEO C-TPAT WEEE RoHS EMC: CE TAA Windows 7 32 bit 64 bit Editions Windows Server 2008 32 bit 64 bit editions Windows Vista 32 bit 64 bit editions Windows Server 2003 32 bit 64 bit editions Windows XP 32 bit 64 bit editions																		
General	PCB Layers Power Consumption Weight Size	4 awaiting 0.085 kg 134l x 18w x 120h mm																		
Box Content	Packaging Card	Installation CD including manual, Microsoft signed drivers & utilities uPCI 2xRS232 POS 1A No Cable; Integrated Connector																		
Product Support 	Warranty Support	Lifetime (online registration required) Lifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team																		
Additional 	OEM option Made In Customisable	Available for bulk buy OEM Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards “Manufacturer of the Year” Brainboxes operate a “Perfect Fit Custom Design” policy for volume users. More Info: sales@brainboxes.com																		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Brainboxes:](#)

[UP-880](#)